


































READING AND WRITING RANGES DTM / DTC (ON AIR)

Device	<div style="display: flex; justify-content: space-between; font-size: 0.8em; font-weight: normal;"> DTM424 (CANopen) DTM425 (CANopen) DTM426 (J1939) DTM427 (J1939) DTM428 (CANopen) DTM434 (CANopen) DTM435 (CANopen) DTM436 (J1939) DTM437 (J1939) DTC510 (CANopen) </div>											
	Picture	Dimension										
			M18 x 1 L = 70	M18 x 1 L = 70	M18 x 1 L = 70	M18 x 1 L = 70	M18 x 1 L = 58	M30 x 1,5 L = 70	M30 x 1,5 L = 70	M30 x 1,5 L = 70	M30 x 1,5 L = 70	40 x 40 x 54
E80341		D 47 x 10	6	4	6	4	4	25	40	25	40	70
E80342		D 34 x 6	6	25	6	25	25	20	30	20	30	45
E80343		90 x 34 x 7	0	20	0	20	20	15	25	15	25	50
E80344		D 16 x 3.0	10	25	10	25	25	20	35	20	35	45
E80347		M5 x 16	0	10	0	10	10	5	15	5	15	25
E80348		18 x 33 x 16,9	0	10	0	10	10	5	15	5	15	20
E80349		D 20 x 3	10	30	10	30	30	25	35	25	35	50
E80370		D 30 x 3	10	30	10	30	30	25	40	25	40	60
E80371		D 30 x 3	15	40	15	40	40	30	50	30	50	65
E80377		D 20 x 3	12	30	12	30	30	25	40	25	40	50
E80379		80 x 50	20	65	20	65	65	50	85	50	85	120
E80380		D 30 x 3	10	30	10	30	30	25	40	25	40	65
E80381		D 4,3 x 3,6	2	5	2	5	5	5	10	5	10	10
E80382		65 x 30	10	40	10	40	40	30	50	30	50	65
E80383		D 50 x 3	10	45	10	45	45	35	60	35	60	80
E80384		D 50 x 3	15	50	15	50	50	35	65	35	65	90
E80385		D 4 x 21.7	5	20	5	20	20	15	30	15	30	40
E80387		40 x 31 x 4,8	15	40	15	40	40	30	45	30	45	60
E80388		D 12 x 2	5	15	5	15	15	10	15	10	15	15
E80400		51 x 51 x 6.5	15	50	15	50	50	40	65	40	65	100
E80404		D 22 x 3	6	16	6	16	16	15	20	15	20	30
E80406		D 7.5 x 1	10	20	10	20	20	15	25	15	25	30
E80407		85,6 x 53,98 x 0,8	20	65	20	65	65	50	85	50	85	120