



Article no longer available - archive entry

Alternative articles: DD2503

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

Application

Application	pulse evaluation system with microprocessor for frequency; rotational speed; speed; pulses and machine cycles
-------------	--

Electrical data

Nominal voltage AC	[V]	< 230
Nominal voltage DC	[V]	24
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	50...60
Power consumption	[W]	3

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1; Number of relay outputs: 2
------------------------------	---

Outputs

Number of relay outputs	2
Contact rating	8 A (1250 VA / 250 V AC)
Number of analogue outputs	1
Analogue current output	[mA] 4...20
Max. load	[Ω] 500



MONITOR

MONITOR/FR-1 /230VAC

Measuring/setting range		
Setting range Hz	[Hz]	0.1...1000
Setting range	[Imp/min]	1...60000
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Max. relative air humidity	[%]	75
Protection		IP 50
Protection rating terminals		IP 20
Tests / approvals		
EMC	EN 61010	: 2001
	EMV 89/336/EWG	
	EN 61000-6-3	: 2007
	EN 61000-6-2	: 2005
Mechanical data		
Weight	[g]	0.365
Housing		housing for DIN rail mounting
Materials		plastics
Displays / operating elements		
Display	switching status	LED, green
		LCD display
Remarks		
Remarks	The unit complies with overvoltage category II; pollution degree 2	
Electrical connection		
dual-chamber terminals: 2 x ...2.5 mm²		
1	DC supply voltage (L-)	
2	DC supply voltage (L+)	
3	current supply transistor outputs (L+)	
4	sensor signal pnp	
5	DC Sensor supply (L+)	
6	DC Sensor supply (L-)	
7	AC supply voltage	
8	AC supply voltage	
9	not used	
10	sensor signal npn	
11	not used	
12	not used	
13	relay 1 common	
14	relay 1 normally open	
15	relay 1 normally closed	
16	transistor output 1 pnp	
17	reset 1 pnp	
18	reset 2 pnp	
19	relay 2 common	
20	relay 2 normally open	
21	relay 2 normally closed	
22	analogue output (+)	
23	analogue output (-)	
24	transistor output 2 pnp	