


Fibre optic through-beam sensor

FE-00-P-A-M4



Application

Function principle	Through-beam sensor
Application	Small bending radius

Detection zone

Range with fibre-optic amplifier type	OCF; OKF; OOF; OUF
---------------------------------------	--------------------

OCF (High Power)

Range of fibre optics [mm]	790
----------------------------	-----

OKF

Range of fibre optics [mm]	120
----------------------------	-----

OOF

Range of fibre optics [mm]	400
----------------------------	-----

OUF

Range of fibre optics [mm]	120
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Weight [g]	41
Version of sensing head	straight
Sensing head thread	M4

E20059



Fibre optic through-beam sensor

FE-00-P-A-M4

Sensing head length	[mm]	15
Total length	[mm]	600
Min. bending radius	[mm]	10
Fibre arrangement		
Materials		Adapter: PPE
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		PVC

Accessories

Items supplied	hexagon nuts: 4 x M4
	tooth lock washers: 4
	knurled nut: 1 x M11

Remarks

Pack quantity	1 pcs.
---------------	--------