


Inductive AS-Interface sensor

IGK2012-ASI /M/US-104



Product characteristics

Electrical design	AS-i
Sensing range [mm]	12
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 60

Application

Special feature	Gold-plated contacts
Application	Use in machine tools, coolants and lubricants

Electrical data

Operating voltage [V]	26.5...31.6 DC
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	1000

Outputs

Electrical design	AS-i
Switching frequency DC [Hz]	100

Detection zone

Sensing range [mm]	12
Real sensing range S_r [mm]	$12 \pm 10 \%$
Operating distance [mm]	0...9.7

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.45 / copper: 0.35
Hysteresis [% of S_r]	1...20
Switch point drift [% of S_r]	-10...10

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 68; ("Coolant")



Inductive AS-Interface sensor

IGK2012-ASI /M/US-104

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	1565
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	File number UL	E174191

AS-i classification						
AS-i version		2.1				
Extended addressing mode		yes				
AS-i I/O configuration [hex]		0				
AS-i ID code [hex]		A.F				
AS-i certificate		57301				
Assignment of the data bits		Designation	switching signal	not used	not used	not used
		status = 0	target outside the active zone	-	-	-
		status = 1	target within the active zone	default value	default value	default value

Mechanical data	
Weight	[g] 46.4
Housing	threaded type
Mounting	non-flush mountable
Dimensions	[mm] M18 x 1 / L = 60
Thread designation	M18 x 1
Materials	threaded sleeve: stainless steel (316L/1.4404); sensing face: LCP uncoloured; lock nuts: brass

Displays / operating elements		
Display	switching status	4 x 90° LED, yellow
	function	1 x LED, red

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated





Inductive AS-Interface sensor

IGK2012-ASI /M/US-104

Connection

