




Capacitive sensor

KI-3200NFPKGP2T/US



- 1 LED ring
- 2 programming buttons



Product characteristics		
Electrical design		PNP
Output function		normally open / normally closed; (selectable)
Sensing range	[mm]	20
Communication interface		IO-Link
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 90
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 20
Protection class		II
Reverse polarity protection		yes
Measuring principle		capacitive
Outputs		
Electrical design		PNP
Output function		normally open / normally closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	10
Short-circuit proof		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	20
Accuracy / deviations		
Hysteresis	[% of Sr]	1...15



Capacitive sensor

KI-3200NFPKGP2T/US

Switch point drift	[% of Sr]	-20...20
--------------------	-----------	----------

Interfaces

Communication interface	IO-Link	
Transmission type	COM1 (4,8 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor	
SIO mode	yes	
Min. process cycle time	[ms]	101
Supported DeviceIDs	Type of operation	DeviceID
	default	388

Operating conditions

Ambient temperature	[°C]	-25...80
Note on ambient temperature	temperature of the sensing face: -25...110 °C	
Protection	IP 65; IP 67	

Tests / approvals

EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance	EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF	[years]	663

Mechanical data

Weight	[g]	88
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 90
Thread designation	M30 x 1.5	
Materials	housing: PBT; pushbuttons: TPE-U; LED window: PC	

Displays / operating elements

Display	switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

KI5083



Capacitive sensor


KI-3200NFPKGP2T/US

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection



4: OUT / IO-Link