









ecolink features	EVC	EVT	EVF	EVM	EVW	EVS	ENC..A	EVC..A
								
Good resistance to oils, grease and coolants	X			X	X		X	X
Good resistance to cleansing agents and disinfectants in the food industry		X	X					
Corrosion resistance (stainless steel nut)		X	X	X				X
Good resistance to UV radiation	X			X	X		X	X
Optimum sealing even when fastened by hand	X	X	X	X	X	X	X	X
High protection rating IP 67 / IP 68 / IP 69K	X	X	X	X	X		X <sup>1</sup>	X <sup>1</sup>
Type M8 with innovative profiled sealing ring	X	X		X	X			
Type M12 with mechanical end stop	X	X	X	X	X	X	X	X
Permanent vibration protection with saw tooth contour	X	X	X	X	X	X	X	X
Drag chain and torsion resistant cable	X	X	X	X	X	X		
Free from silicone	X	X	X	X	X	X	X	X
Free from halogen	X		X	X	X		X	X
UL & CSA approval	X	X	X	X	X	X		
Ecolab certified		X	X					
Group II, category 1D / 1G							X	
Group II, category 2D / 3G								X

\*1 Note the data sheet!

