



Connecting cable with socket

ADOGG030--S0010A03

Article no longer available - archive entry

No scale drawing available

Application

Special feature	Halogen-free
-----------------	--------------

Electrical data

Operating voltage	[V]	< 60 AC / < 75 DC
-------------------	-----	-------------------

Protection class	III
------------------	-----

Operating conditions

Ambient temperature	[°C]	-25...90
---------------------	------	----------

Protection	IP 65
------------	-------

Mechanical data

Dimensions	[mm]	8 x 8 x 31
------------	------	------------

Materials	TPU
-----------	-----

Moulded-body material	TPU
-----------------------	-----

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 10 m, PUR / PVC, Halogen-free, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU




E10623



Connecting cable with socket

ADOGG030--S0010A03

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue