


# EVF549



## Ethernet connection cable

VSTGN040VAS00,5P04STGP040--S



### Application

Special feature	Free from silicone; Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
Design	Ethernet cable, D-coded
Application	Industrial Ethernet; CAT5/CAT5e; 100 Mbit/s; hygienic and wet areas in the food industry
Free from silicone	yes

### Electrical data

Operating voltage	[V]	30 AC / 60 DC
Protection class		III
Max. current load total	[A]	1.5

### Operating conditions

Ambient temperature	[°C]	-25...100
Note on ambient temperature		Ethernet RJ45 connector: -40...70 °C
Ambient temperature (moving)	[°C]	0...80
Protection		IP 65; IP 67; IP 68; IP 69K; (M12 plug / RJ45 plug: IP 20)

# EVF549



## Ethernet connection cable

VSTGN040VAS00,5P04STGP040--S

Mechanical data		
Weight [g]	58.4	
Materials	brass nickel-plated; housing: PP Halogen-free	
Moulded-body material	PP / PC	
Material nut	stainless steel (1.4404 / 316L)	
Tightening torque [Nm]	Lock nut: 0,6...1,2	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 15 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>
	bending cycles	> 1 Mio.
	torsional strain	± 180 °/m

Remarks	
Remarks	Take into account the maximum value of the counterpart!
Pack quantity	1 pcs.

### Electrical connection - plug M12


Connector: 1 x M12, straight; coding: D; Moulded body: PP; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated



### Electrical connection

Cable: 0.5 m, MPPE, Halogen-free, grey, Ø 6.5 mm, shielded; PROFINET Type C; 4 x 0.34 mm<sup>2</sup> (7 x Ø 0.25 mm)

### Connection



### Electrical connection - plug RJ45

Connector: 1 x RJ45, straight; Moulded body: PC; Contacts: gold-plated

# EVF549



## Ethernet connection cable

VSTGN040VAS00,5P04STGP040--S

