




Article no longer available - archive entry




Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	40; (24 V)
Outputs		
Total number of outputs		1
Electrical design		PNP/NPN
Output function		light-on/dark-on mode; (parameterisable)
Switching frequency DC	[Hz]	100
Operating conditions		
Ambient temperature	[°C]	0...70
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Weight	[g]	135.5
Housing		housing for DIN rail mounting
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, red
	setting aid	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

Electrical connection

terminals: 12 x ...2.5 mm²

Connection



- 1 blocking signal
- 2 transmitter
- 3 receiver
- 4 Output function
- OUT transistor outputs