

## Fibre optic diffuse reflection sensor

FT-00-A-A-M6/1,8m

Article no longer available - archive entry

Alternative articles: E20124

When selecting an alternative article and accessories please note that technical data may differ!



## Application

Function principle

Diffuse reflection sensor

## Detection zone

Range with fibre optic amplifier type

OKF; OUF

## OKF

Range fibre optics

[mm]

35

## OUF

Range fibre optics

[mm]

35

## Operating conditions

Ambient temperature

[°C]

-40...290

## Mechanical data

Version of sensing head

straight

Sensing head thread

M6

Sensing head length

[mm]

35

Total length

[mm]

1800

E20243



Fibre optic diffuse reflection sensor

FT-00-A-A-M6/1,8m

|                       |      |              |
|-----------------------|------|--------------|
| Min. bending radius   | [mm] | 20           |
| Materials             |      | Adapter: ABS |
| Fibre material        |      | glass        |
| Fibre head material   |      | aluminium    |
| Fibre sheath material |      | aluminium    |
| Remarks               |      |              |
| Pack quantity         |      | 1 pcs.       |