




AS-Interface control cabinet module

CabinetModule 4DO T C

Article no longer available - archive entry



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 40
Max. current load total	[A]	4

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 4
------------------------------	------------------------------

Outputs

Electrical design	PNP
Number of digital outputs	4
Circuit	PNP
Voltage range DC	[V] 10...30; (to PELV)
Max. current load per output	[mA] 1000
Short-circuit proof	yes
Electrically separated	yes

Operating conditions

Ambient temperature	[°C] -25...70
Protection	IP 20

Tests / approvals


EMC	EN 50295
-----	----------



AS-Interface control cabinet module

CabinetModule 4DO T C

AS-i classification		
AS-i profile		S-8.0
AS-i I/O configuration	[hex]	8
AS-i ID code	[hex]	0
Mechanical data		
Type of mounting	mounting on DIN rail and panel; string mounting possible	
Materials	PA; PVC	
Displays / operating elements		
Display	switching status	LED, yellow
	operation	LED, green
	short circuit	LED, red
Remarks		
Remarks	Do not connect any of the following points to an external potential: I-, I+, I1, I2, I3, I4	
Pack quantity	1 pcs.	
Electrical connection		
Connection		



A+	AS-i+
A-	AS-i -
E+	actuator supply +24V
E-	actuator supply 0V
O1...O4	switching output actuator 1...4