




Welding adapter for process sensors

WELDING ADAPT D85 G1 V4A 3A



- 1 G1 Internal thread Aseptoflex Vario
 2 Leakage port
 3 sealing area



EC 1935/2004 EHEDG Certified



Application	
Design	with leakage port
Installation	for thick wall thicknesses and for unfavourable welding conditions; for tank bottom and wall
Pressure rating [bar]	16
Note on pressure rating	for the connection sensor - adapter
Tests / approvals	
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.
Mechanical data	
Weight [g]	362
Materials (wetted parts)	stainless steel (316L/1.4435) ; surface characteristics : Ra<0,4 / R
Sensor connection	G 1 internal thread Aseptoflex Vario
Process connection	welding adapter Ø 85 mm
Sealing	Gasket
Accessories	
Items supplied	O-ring: 1 x 24 x 2, EPDM, E30054
Accessories (optional)	O-ring: 1 x 24 x 2, FKM, E30123
Remarks	
Pack quantity	1 pcs.