



Article no longer available - archive entry

Alternative articles: DX2002

When selecting an alternative article and accessories please note that technical data may differ!

# No scale drawing available



## Application

Application	universal evaluation and display for all physical units which can be derived from pulse sequences
-------------	---

## Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	200

## Outputs

Analogue current output	[mA]	4...20
Analogue voltage output	[V]	0...10

## Operating conditions

Ambient temperature	[°C]	0...45
Protection		IP 44; (on the front)

## Mechanical data

Type of mounting	panel cutout: 91 x 43 mm
------------------	--------------------------

## Displays / operating elements

Display	7-segment LED display, red 6-digit 15 mm
	4 x LED, red

## Electrical connection

### Connection