




Through-beam sensor receiver

OJE-FPKG/FO/0,15M/US



1 pushbutton without function



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		Gold-plated contacts
Function principle		Through-beam sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 12
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660
Outputs		
Electrical design		PNP
Output function		light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC	[V]	2.5



Through-beam sensor receiver

OJE-FPKG/FO/0,15M/US

Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	1200
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Transmitter / receiver		receiver
Range	[m]	< 10
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 67

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	968

Mechanical data

Weight	[g]	40.55
Housing		rectangular
Dimensions	[mm]	35 x 24 x 11
Materials		housing: ABS; fixture: diecast zinc; LED window: SEPS; pushbutton: SEPS
Lens material		glass
Lens alignment		front lens

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red
Electronic lock		yes

Accessories

Items supplied		Basic clip: 1, E20964
		screws: 2 x M3 x 16
		spring washers: 2
		Nuts: 2

Remarks

Remarks		operating voltage "supply class 2" according to cULus
Pack quantity		1 pcs.

Through-beam sensor receiver

OJE-FPKG/FO/0,15M/US


Electrical connection

Cable: 0.15 m, PVC

Connector: 1 x M12; coding: A; Moulded body: Hytrel 8068; Locking: stainless steel (316L/1.4404); Contacts: gold-plated



Connection



2 Teach



Through-beam sensor receiver

OJE-FPKG/FO/0,15M/US

Diagrams and graphs

excess gain graph

