


TS2689



Temperature cable sensor with screw-in sensor

TS-200KLKM06...../US



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	threaded connection M6 external thread	

Application

Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Installation	surface mount RTD for solid bodies

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy	[K]	$\pm (0,15 K + 0,002 \times t)$
----------	-----	-----------------------------------

Response times

Dynamic response T05 / T09	[s]	3 / 9; (to DIN EN 60751)
----------------------------	-----	--------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF	[years]	11415.5
------	---------	---------

Mechanical data

Weight	[g]	86.75
Housing	screw-in sensor	
Dimensions	[mm]	M6 / L = 26
Thread designation	M6	
Materials	stainless steel (316L/1.4404)	
Process connection	threaded connection M6 external thread	

Remarks

Pack quantity	1 pcs.
---------------	--------

TS2689



Temperature cable sensor with screw-in sensor

TS-200KLKM06...../US

Electrical connection

Cable: 2 m, PUR

Connector: 1 x M12; coding: A



Connection

