




Fibre optic through-beam sensor

FE-30-P-A-R3/2M

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Detection zone

Range with fibre-optic
amplifier type

OIF

OIF

Range of fibre optics

[mm]

80

Operating conditions

Ambient temperature

[°C]

-20...80

Mechanical data

Version of sensing head

angled

Total length

[mm]

2000

Min. bending radius

[mm]

30

Materials

Adapter: PA

Fibre material

glass

Fibre head material

aluminium

Fibre sheath material

PVC

Accessories

Items supplied

E20104

E20218



Fibre optic through-beam sensor

FE-30-P-A-R3/2M

Remarks	
Pack quantity	1 pcs.