


DV1510



5-segment light tower

LED-Tower-5/Std/Bracket+Buz



1 buzzer



Application	
Application	signalling machine conditions
Electrical data	
Operating voltage [V]	18...30 DC; (to SELV/PELV)
Nominal voltage DC [V]	24
Current consumption [mA]	< 200
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 6

DV1510



5-segment light tower

LED-Tower-5/Std/Bracket+Buz

Inputs		
Number of digital inputs		6
Input current High	[mA]	6
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
SIO mode		yes
Required master port type		A
Min. process cycle time	[ms]	8
Supported DeviceIDs	Type of operation	DeviceID
	Default	850
	Status B	1076
Operating conditions		
Ambient temperature	[°C]	-25...50
Storage temperature	[°C]	-40...75
Max. relative air humidity	[%]	90
Air pressure	[kPa]	< 106
Max. height above sea level	[m]	2000
Protection		IP 54
Tests / approvals		
MTTF	[years]	76
Mechanical data		
Weight	[g]	647.5
Type of mounting		mounting base
Dimensions	[mm]	Ø 70 / L = 384
Materials		housing: ABS; lens: PC
Displays / operating elements		
Display	status	1 x LED, green
	LED segment	5 x 4 LED
Acoustic signal		buzzer
Max. sound pressure	[dB]	85
Accessories		
Accessories (optional)		mounting base, E89060
		wall bracket, E89061
		mounting adapter, E89063
		bracket with lateral cable entry, E89064
		mounting tube, E89065
		mounting tube, E89066
		mounting tube, E89067
Remarks		
Remarks		For further information please see the operating instructions.
Pack quantity		1 pcs.

DV1510




5-segment light tower

LED-Tower-5/Std/Bracket+Buz

Electrical connection - plug

Connector: M12; coding: A; Contacts: 8




Connection

1	digital input LED segment 5
2	buzzer
3	digital input LED segment 3
4	digital input LED segment 2
5	power supply
6	digital input LED segment 1
7	digital input LED segment 4
8	IO-Link (C/Q)

Diagrams and graphs

Installation





DV1510

5-segment light tower

LED-Tower-5/Std/Bracket+Buz



Installation



- 1 mounting on a horizontal surface
- 2 mounting on a vertical surface


DV1510

5-segment light tower

LED-Tower-5/Std/Bracket+Buz



base mounting



1 E89060 not supplied

2 E89065, E89066, E89067 not supplied


DV1510

5-segment light tower

LED-Tower-5/Std/Bracket+Buz



wall mounting



- 1 E89060 not supplied
- 2 E89065, E89066, E89067 not supplied
- 3 E89061 not supplied