


E60208



Flexible coupling for encoders

COUPLING 30-10-12-38-KV



Mechanical data

Weight	[g]	58
Dimensions	[mm]	Ø 30 / L = 38
Materials		aluminium
External diameter D	[mm]	30
Inside diameter 1	[mm]	10
Inside diameter 2	[mm]	12,7 mm / 1/2" / 1/2 inch
Length L	[mm]	38
Depth of the clamping hub	[mm]	10
Clamping screw	[mm]	M4 x 12 - ISO 4762 (2 x)
Max. revolution, mechanical [U/min]		6000
Max. axial shaft misalignment [mm]		± 0,5
Max. radial shaft misalignment [mm]		± 0,35
Max. angular displacement [°]		± 4,0

Remarks

Remarks	The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C.
	The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation.
Pack quantity	1 pcs.