



AS-Interface gateway

BACKPLANE MASTER-COMPACTLOGIX

No scale drawing available

Application		
Application		ASI master for CompactLogix and MicroLogix 1500 PLC platforms
Electrical data		
Operating voltage		[V] 30 DC; (AS-i)
Current consumption		[mA] 5 V DC: 450 mA; AS-i: 100 mA
Number of AS-i masters		1
Interfaces		
Communication interface		RS232
RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Connector type		RJ11
Usage type		programming
Operating conditions		
Ambient temperature		[°C] 0...55
Storage temperature		[°C] -25...85
Protection		IP 20
AS-i classification		
AS-i version		3.0
Mechanical data		
Weight		[g] 226.796
Displays / operating elements		
Display		LED bar display
Remarks		
Remarks		Configuration is handled through Allen-Bradleys' RSLogix software.
Pack quantity		1 pcs.