



No scale drawing available



Application	
Application	AS-i master for ControlLogix PLC platform
Electrical data	
Operating voltage [V]	30 DC; (AS-i)
Current consumption [mA]	5,1 V DC: 390 mA; 24 V DC: 150 mA; AS-i 1: 70 mA; AS-i 2: 70 mA
Number of AS-i masters	2
Interfaces	
Communication interface	RS232
RS232	
Number of R232 interfaces	1
Transmission rate	9600...115200 Baud
Connector type	RJ11
Usage type	programming
Operating conditions	
Ambient temperature [°C]	0...55
Storage temperature [°C]	-25...85
Protection	IP 20
AS-i classification	
AS-i version	3.0
Mechanical data	
Weight [g]	305
Displays / operating elements	
Display	LED bar display

# U71005



## AS-Interface gateway ControlLogix

AS-i MASTER (A-B)

Remarks	
Remarks	Configuration is handled through Allen-Bradleys' RSLogix software.
Pack quantity	1 pcs.