


Process adapter for SMS pipe fitting

ADAPT IFM-SMS DN50/2"



1 sealing edge

EC 1935/2004 FCM 

Application		
Pressure rating	[bar]	25
Tests / approvals		
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	
Mechanical data		
Weight	[g]	267
Materials (wetted parts)	stainless steel (316L/1.4435) ; surface characteristics : Ra<0,4 / Rz 4	
Sensor connection	G 1 internal thread Aseptoflex Vario	
Process connection	SMS pipe fitting DN50 (2")	
Sealing	metal to metal	
Hygienic equipment class to DIN 11866	H4	
Remarks		
Pack quantity	1 pcs.	