


E40240



Mounting adapter for flow sensors

ADAPT G2 FLANGE ADJUSTABLE



ACS

Application	
Design	for flow sensors Typ SM2, SM9
Installation	SM2 SM9
Pressure rating [bar]	16
Mechanical data	
Weight [g]	2255.5
Type of mounting	Adapter; (rotatable)
Materials	flange: stainless steel (1.4301 / 304); Adapter: stainless steel (316Ti/1.4571); O-ring: EPDM 47,22 x 3,53 mm
Sensor connection	G 2

E40240



Mounting adapter for flow sensors

ADAPT G2 FLANGE ADJUSTABLE

Process connection	flange DN50 according to DIN2642 / EN1092-1 type 2
Accessories	
Items supplied	O-rings: 2
Remarks	
Pack quantity	2 pcs.