



Article no longer available - archive entry

replaced by: DN0200

No scale drawing available



Product characteristics

Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110

Application

Application	Power supply and signal evaluation
-------------	------------------------------------

Electrical data

Nominal voltage AC [V]	< 110
Nominal voltage tolerance [%]	10
Nominal voltage tolerance 2 [%]	10
Nominal frequency AC [Hz]	47...63
Auxiliary energy for sensors DC [V]	24; ($\pm 5\%$, ≤ 40 mA)

Outputs

Contact rating	4 A / 625 VA / 250 V AC
----------------	-------------------------

Operating conditions

Ambient temperature [°C]	0...50
Protection	IP 40
Protection rating terminals	IP 20

Mechanical data

Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110
Materials	plastics

DN0213



Switching amplifier

N600/110VAC/0,08A

Displays / operating elements		
Display	switching status	LED, green
	operation	1 x LED, green

Electrical connection
terminals: ...4 mm ²

Connection

Article no longer available - archive entry

replaced by: DN0200