


Connecting cable with socket

ADOGF030MSS0008B03

Article no longer available - archive entry



Electrical data

Operating voltage	[M]	< 60 AC / < 75 DC
Protection class		III

Operating conditions

Ambient temperature	[°C]	-25...90
Protection		IP 67

Mechanical data

Materials	TPU
Moulded-body material	TPU
Material nut	brass, nickel-plated

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 8 m, PUR, orange, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E10974



Connecting cable with socket

ADOGF030MSS0008B03

Connection



BN =	Core colours :	brown
BK =		black
BU =		blue