




Connecting cable with plug

ASTGH050MSA0002C02



Application		
Special feature	Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability	
Application	CAN bus	
Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-20...80
Storage temperature	[°C]	-40...80
Protection	IP 68	
Mechanical data		
Weight	[g]	167.8
Dimensions	[mm]	14.5 x 14.5 x 48.5
Materials	PUR	
Moulded-body material	PUR	
Material nut	brass, nickel-plated	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	bending radius for fixed installation	min. 5 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
	bending cycles	> 1 Mio.
Remarks		
Pack quantity	1 pcs.	

E11598



Connecting cable with plug

ASTGH050MSA0002C02

Electrical connection


Cable: 2 m, PUR, Halogen-free, lilac, Ø 6.8 mm, shielded; RD / BK: 2 x 0.25 mm² (19 x Ø 0.13 mm) + WH / BU: 2 x 0.34 mm² (19 x Ø 0.16 mm) + screen: 1 x 0.34 mm² (19 x Ø 0.16 mm)

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.5 Nm



Connection



	Core colours :
BK =	black
BU =	blue
RD =	red
WH =	white
screen =	screen