



Fibre optic diffuse reflection sensor

FT-00-M-V-M6/2M

Article no longer available - archive entry

Alternative articles: E20570

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Detection zone

Range with fibre optic amplifier type	OKF
---------------------------------------	-----

OKF

Range fibre optics [mm]	10
-------------------------	----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	2000
Min. bending radius [mm]	20
Fibre material	acrylic
Fibre head material	stainless steel (303/1.4305)
Fibre sheath material	metal silicone

Remarks

Pack quantity	1 pcs.
---------------	--------