




Fibre optic diffuse reflection sensor

FT-18-P-A-M6

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Application		For use in industrial environments
Detection zone		
Range with fibre optic amplifier type		OGF
OGF		
Range fibre optics	[mm]	15
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Weight	[g]	50.2
Version of sensing head		straight
Sensing head thread		M6
Sensing head length	[mm]	35
Total length	[mm]	600
Min. bending radius	[mm]	20
Fibre arrangement		Ⓜ
Materials		Adapter: PPE

E20383



Fibre optic diffuse reflection sensor

FT-18-P-A-M6

Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	PVC
Accessories	
Items supplied	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 2
Remarks	
Pack quantity	1 pcs.