

Fibre optic through-beam sensor

FE-00-S-V-M4/0,4M

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Detection zone

Range with fibre-optic
amplifier type

OKF; OUF

OKF

Range of fibre optics

[mm]

120

OUF

Range of fibre optics

[mm]

120

Operating conditions

Ambient temperature

[°C]

-20...80

Mechanical data

Version of sensing head

straight

Sensing head thread

M4

Sensing head length

[mm]

15

Total length

[mm]

400

Min. bending radius

[mm]

20

Materials

Adapter: ABS

Fibre material

glass

E20394



Fibre optic through-beam sensor

FE-00-S-V-M4/0,4M

Fibre head material	stainless steel (303/1.4305)
Fibre sheath material	silicone
Remarks	
Pack quantity	1 pcs.