


Fibre optic diffuse reflection sensor

FT-11-M-V-M6/5M

Article no longer available - archive entry



Application

Function principle

Diffuse reflection sensor

Detection zone

Range with fibre optic
amplifier type

OB5030

OB50

Range fibre optics

[mm]

8

Operating conditions

Ambient temperature

[°C]

-20...150

Mechanical data

Version of sensing head

straight

Sensing head thread

M6

Sensing head length

[mm]

45

Total length

[mm]

5000

Min. bending radius

[mm]

20

Fibre material

glass

Fibre head material

stainless steel (1.4305 / 303)

Fibre sheath material

metal silicone

E21040



Fibre optic diffuse reflection sensor

FT-11-M-V-M6/5M

Remarks	
Pack quantity	1 pcs.