


# EVF250



## Connection cable

VDOGF040VAS0001P04STGH040VAS



### Application

|                    |                                                                                |
|--------------------|--------------------------------------------------------------------------------|
| Special feature    | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Application        | hygienic and wet areas in the food industry                                    |
| Free from silicone | yes                                                                            |

### Electrical data

|                         |     |                                           |
|-------------------------|-----|-------------------------------------------|
| Operating voltage       | [V] | < 50 AC / < 60 DC; (cULus: 30 AC / 30 DC) |
| Protection class        |     | III                                       |
| Max. current load total | [A] | 3                                         |

### Operating conditions

|                              |      |                             |
|------------------------------|------|-----------------------------|
| Ambient temperature          | [°C] | -25...80                    |
| Ambient temperature (moving) | [°C] | 5...80                      |
| Protection                   |      | IP 65; IP 67; IP 68; IP 69K |

### Tests / approvals

|             |              |         |
|-------------|--------------|---------|
| UL approval | power supply | Class 2 |
|-------------|--------------|---------|

### Mechanical data

|                        |      |                                         |
|------------------------|------|-----------------------------------------|
| Weight                 | [g]  | 53.4                                    |
| Dimensions             | [mm] | 15.5 x 15.5 x 49.5                      |
| Materials              |      | housing: PP Halogen-free; Sealing: EPDM |
| Material nut           |      | stainless steel (316L/1.4404)           |
| Drag chain suitability |      | yes                                     |



## Connection cable

VDOGF040VAS0001P04STGH040VAS

|                        |                                 |                                                                                                |
|------------------------|---------------------------------|------------------------------------------------------------------------------------------------|
| Drag chain suitability | bending radius for flexible use | min. 10 x cable diameter                                                                       |
|                        | travel speed                    | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup> |
|                        | bending cycles                  | > 1 Mio.                                                                                       |
|                        | torsional strain                | ± 180 °/m                                                                                      |

### Remarks

Pack quantity

1 pcs.

### Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Locking: stainless steel (316L/1.4404); Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



### Electrical connection

Cable: 1.0 m, MPPE, Halogen-free, grey, Ø 4.9 mm; 4 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Connection



### Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Locking: stainless steel (316L/1.4404); Contacts: gold-plated; Tightening torque: 0.3...0.5 Nm

