

## IO-Link parameter setting software

LR DEVICE (Download)

Article no longer available - archive entry

Alternative articles: QMP010

When selecting an alternative article and accessories please note that technical data may differ!



## Application

Application

online and offline parameter setting of IO-Link devices

Function

parameter setting of IO-Link devices and ifm IO-Link masters; graphic representation of process values for device set-up and diagnosis; IODD management

## Software / programming

Language

German; English; Spanish; French; Italian;  
Japanese; Korean; Portuguese; Russian; Chinese

Data carrier

download



## IO-Link parameter setting software

LR DEVICE (Download)

|                            |                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| Type of licence            | single licence                                                                                                                              |
| Licence class              | full version                                                                                                                                |
| <b>System requirements</b> |                                                                                                                                             |
| Min. CPU cycle             | 2 GHz                                                                                                                                       |
| Min. number of CPU cores   | 2                                                                                                                                           |
| Min. RAM                   | 2 GB                                                                                                                                        |
| Min. hard disk memory      | 5 GB                                                                                                                                        |
| Min. graphic resolution    | 1680 x 1050                                                                                                                                 |
| Required device interface  | LAN Adapter - RJ45; USB                                                                                                                     |
| Operating system           | Microsoft Windows 8.1; Microsoft Windows 10; Microsoft Windows Server 2012; Microsoft Windows Server 2012 R2; Microsoft Windows Server 2016 |
| Web browser                | Google Chrome; Mozilla Firefox; Microsoft Internet Explorer 11; Microsoft Edge                                                              |