



Licence for the operation of moneo in virtualisation environments

moneo vAppliance License



Application	
Application	Virtual appliance for operating the moneo software in an existing IT infrastructure moneo software preinstalled incl. management system for appliance maintenance
Configuration	Integration of the .OVF file into the virtualisation environment and subsequent configuration in the AMS (appliance management system)
Compatibility	VMware vSphere 7.0 or more recent version Microsoft Hyper-V 2019 or more recent version
Connectivity	interfaces for sensor and IT network
Maintenance and support	incl. maintenance and support until the end of the subsequent year
Software / programming	
Language	English
Data carrier	download



Licence for the operation of moneo in virtualisation environments

moneo vAppliance License	
Type of licence	single licence
Licence class	full version
System requirements	
Min. CPU cycle	1,8 GHz
Min. number of CPU cores	4
Min. RAM	8 GB
Min. graphic resolution	1920 x 1080
Network card	2 x Ethernet 1 Gbit
Network protocol	Ethernet TCP/IP
Operating system	VMware vSphere 7.0; Microsoft Hyper-V 2019; (or more recent version)
Web browser	Google Chrome; Mozilla Firefox; (supported versions: see current release notes)
Remarks	
Remarks	licences required for the operation of moneo products have to be ordered separately