


AS-Interface module

ASI-MODUL-OBERTEIL M12 4V

Article no longer available - archive entry

Alternative articles: AC5200

When selecting an alternative article and accessories please note that technical data may differ!



1 panel for labelling



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current load total	[A]	2
Additional voltage supply	[V]	24 DC

Inputs

Power supply	[V]	20...30
--------------	-----	---------

Outputs

Electrical design	AS-i
-------------------	------

Operating conditions

Ambient temperature	[°C]	-40...85
Protection		IP 67

Tests / approvals

EMC	EN 50295
-----	----------

Mechanical data

Type of mounting	AS-i interface to FC lower parts
Materials	PBT

Remarks

Pack quantity	1 pcs.
---------------	--------

AC2000



AS-Interface module

ASI-MODUL-OBERTEIL M12 4V

Electrical connection

contact pins to module lower part, FK / PG:

Connector: M12; coding: A



1	AS-i +
3	AS-i -