

E10462




Connection cable

VDOGH040MSS00,3A04STGH040MSS

Article no longer available - archive entry


Alternative articles: EVC010
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	10...30 DC
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Dimensions	[mm]	15 x 15 x 42
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm



E10462




Connection cable

VDOGH040MSS00,3A04STGH040MSS

Electrical connection

Cable: 0.3 m, PUR / PVC, orange; 4 x 0.25 mm² (128 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm

