

E11036



Mounting adapter for capacitive sensors

MOUNTING ADAPTER M30 PVDF



1 O-ring 44 x 2 mm

Application

Pressure rating [bar] 8

Operating conditions

Ambient temperature [°C] -25...110

Mechanical data

Weight [g] 83.4

Dimensions [mm] G 1 1/4 / L = 65

Thread designation G 1 1/4

Materials Adapter: PVDF; Gasket: EPDM

Sensor connection threaded connection M30 x 1,5 internal thread

Process connection threaded connection G 1 1/4 external thread

Remarks

Pack quantity 1 pcs.