




Fibre optic through beam sensor

FE-30-A-A-R6/2M



Application

Function principle Through-beam sensor

Detection zone

Range with fibre optic amplifier type OIF

OIF

Range of fibre optics [mm] 240

Operating conditions

Ambient temperature [°C] -40...290

Mechanical data

Weight [g]	201
Version of sensing head	angled
Sensing head diameter [mm]	6
Total length [mm]	2000
Min. bending radius [mm]	30; (for fixed installation)
Fibre arrangement	●
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	aluminium

E20339



Fibre optic through beam sensor

FE-30-A-A-R6/2M

Accessories	
Accessories (supplied)	E10221
Remarks	
Pack quantity	1 pcs.