

E89123



Digital display

DISPLAY/DY340

Article no longer available - archive entry

Alternative articles: DX2003

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Application

Application	universal evaluation and display for all physical units which can be derived from pulse sequences
-------------	---

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	200

Operating conditions

Ambient temperature	[°C]	0...45
Protection		IP 44; (on the front)

Mechanical data

Type of mounting	panel cutout: 91 x 43 mm
------------------	--------------------------

Displays / operating elements

Display	7-segment LED display, red 6-digit 15 mm
	4 x LED, red

Electrical connection

Connection