



IO-Link parameter setting software

LR DEVICE (USB Stick)

phase-out article

Alternative articles: QMP010

When selecting an alternative article and accessories please note that technical data may differ!



Application

Application	online and offline parameter setting of IO-Link devices
Function	parameter setting of IO-Link devices and ifm IO-Link masters; graphic representation of process values for device set-up and diagnosis; IODD management

Software / programming

Language	German; English; Spanish; French; Italian; Japanese; Korean; Portuguese; Russian; Chinese
Data carrier	USB stick
Type of licence	single licence
Licence class	full version

System requirements

Min. CPU cycle	2 GHz
Min. number of CPU cores	2
Min. RAM	2 GB
Min. hard disk memory	5 GB
Min. graphic resolution	1680 x 1050
Required device interface	LAN Adapter - RJ45; USB
Operating system	Microsoft Windows 8.1; Microsoft Windows 10; Microsoft Windows Server 2012; Microsoft Windows Server 2012 R2; Microsoft Windows Server 2016
Web browser	Google Chrome; Mozilla Firefox; Microsoft Internet Explorer 11; Microsoft Edge

Mechanical data

Weight	[g]	145
--------	-----	-----