




Mounting set for manual valves and ball valves

MOUNTING KIT FOR MANUAL VALVES F03/M4



Application

Design

for types IND, INE

Operating conditions

Ambient temperature

[°C]

-30...80

Mechanical data

Weight

[g]

459

Top flange diameter

[mm]

36

ISO top flange type

F03

Shaft extension

M4

Materials

Mounting plate: plastics; metal parts: stainless steel (1.4301 / 304)

Remarks

Pack quantity

1 pcs.