




Pressure sensor with analogue display

PG-001-REB12-MFRKG/US/ /P

When selecting an alternative article and accessories please note that technical data may differ!



| Product characteristics      |                                                             |                 |                  |
|------------------------------|-------------------------------------------------------------|-----------------|------------------|
| Number of inputs and outputs | Number of digital outputs: 1; Number of analogue outputs: 1 |                 |                  |
| Measuring range              | -0.05...1 bar                                               | -50...1000 mbar | -0.72...14.5 psi |
| Process connection           | threaded connection G 1/2 external thread                   |                 |                  |
| Application                  |                                                             |                 |                  |
| Special feature              | Gold-plated contacts                                        |                 |                  |
| Application                  | for industrial applications                                 |                 |                  |
| Media                        | liquids and gases                                           |                 |                  |
| Medium temperature [°C]      | -25...80                                                    |                 |                  |
| Min. bursting pressure       | 30 bar                                                      | 435 psi         |                  |
| Pressure rating              | 10 bar                                                      | 145 psi         |                  |
| Type of pressure             | relative pressure                                           |                 |                  |
| Electrical data              |                                                             |                 |                  |
| Operating voltage [V]        | 18...32 DC                                                  |                 |                  |



## Pressure sensor with analogue display

PG-001-REB12-MFRKG/US/ /P

|                             |      |                 |
|-----------------------------|------|-----------------|
| Current consumption         | [mA] | < 70; (24 V)    |
| Min. insulation resistance  | [MΩ] | 100; (500 V DC) |
| Protection class            |      | III             |
| Reverse polarity protection |      | yes             |
| Power-on delay time         | [s]  | 6               |
| Integrated watchdog         |      | yes             |

### Inputs / outputs

|                              |                                                             |
|------------------------------|-------------------------------------------------------------|
| Number of inputs and outputs | Number of digital outputs: 1; Number of analogue outputs: 1 |
|------------------------------|-------------------------------------------------------------|

### Outputs

|                                                      |                                                    |
|------------------------------------------------------|----------------------------------------------------|
| Total number of outputs                              | 2                                                  |
| Output signal                                        | switching signal; analogue signal; (configurable)  |
| Electrical design                                    | PNP/NPN                                            |
| Number of digital outputs                            | 1                                                  |
| Output function                                      | normally open / normally closed; (parameterisable) |
| Max. voltage drop switching output DC [V]            | 2                                                  |
| Permanent current rating of switching output DC [mA] | 250                                                |
| Switching frequency DC [Hz]                          | 75                                                 |
| Number of analogue outputs                           | 1                                                  |
| Analogue current output [mA]                         | 4...20, invertible; (scalable)                     |
| Max. load [Ω]                                        | (Ub - 10 V) / 20 mA                                |
| Short-circuit protection                             | yes                                                |
| Type of short-circuit protection                     | pulsed                                             |
| Overload protection                                  | yes                                                |

### Measuring/setting range

|                      |                   |                   |                  |
|----------------------|-------------------|-------------------|------------------|
| Measuring range      | -0.05...1 bar     | -50...1000 mbar   | -0.72...14.5 psi |
| Set point SP         | -0.046...1.6 bar  | -0.66...23.2 psi  |                  |
| Reset point rP       | -0.05...1.596 bar | -0.72...23.14 psi |                  |
| Analogue start point | -0.05...1.34 bar  | -0.72...19.58 psi |                  |
| Analogue end point   | 0.2...1.6 bar     | 2.9...23.2 psi    |                  |
| In steps of          | 0.002 bar         | 0.02 psi          |                  |

### Accuracy / deviations

|                                    |                        |                                                                                |
|------------------------------------|------------------------|--------------------------------------------------------------------------------|
| Switch point accuracy              | [% of the span]        | < ± 0,5; (Turn down 1:1)                                                       |
| Repeatability                      | [% of the span]        | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)                 |
| Characteristics deviation          | [% of the span]        | < ± 0,25 (BFSL) / < ± 0,5 (LS); (Turn down 1:1; BFSL = Best Fit Straight Line) |
| Hysteresis deviation               | [% of the span]        | < ± 0,25; (Turn down 1:1)                                                      |
| Long-term stability                | [% of the span]        | < ± 0,1; (Turn down 1:1; per 6 months)                                         |
| Temperature coefficient zero point | [% of the span / 10 K] | < ± 0,2; (0...70 °C)                                                           |



## Pressure sensor with analogue display

PG-001-REB12-MFRKG/US/ /P

|                                                        |                                                                                          |                                                                                  |
|--------------------------------------------------------|------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Temperature coefficient span<br>[% of the span / 10 K] | < ± 0,2; (0...70 °C)                                                                     |                                                                                  |
| Response times                                         |                                                                                          |                                                                                  |
| Response time [ms]                                     | < 9                                                                                      |                                                                                  |
| Damping process value dAP [s]                          | 0.01...30                                                                                |                                                                                  |
| Damping for the analogue output dAA [s]                | 0.01...30                                                                                |                                                                                  |
| Step response time analogue output [ms]                | 28                                                                                       |                                                                                  |
| Operating conditions                                   |                                                                                          |                                                                                  |
| Ambient temperature [°C]                               | -20...80                                                                                 |                                                                                  |
| Storage temperature [°C]                               | -40...100                                                                                |                                                                                  |
| Protection                                             | IP 67; IP 69K                                                                            |                                                                                  |
| Tests / approvals                                      |                                                                                          |                                                                                  |
| EMC                                                    | EN 61000-4-2 ESD                                                                         | 4 kV CD / 8 kV AD                                                                |
|                                                        | EN 61000-4-3 HF radiated                                                                 | 10 V/m                                                                           |
|                                                        | EN 61000-4-4 Burst                                                                       | 2 kV                                                                             |
|                                                        | EN 61000-4-5 Surge                                                                       | 0,5/1 kV                                                                         |
|                                                        | EN 61000-4-6 HF conducted                                                                | 10 V                                                                             |
| Shock resistance                                       | DIN IEC 68-2-27                                                                          | 50 g (11 ms)                                                                     |
| Vibration resistance                                   | DIN IEC 68-2-6                                                                           | 20 g (10...2000 Hz)                                                              |
| MTTF [years]                                           | 103                                                                                      |                                                                                  |
| Pressure Equipment Directive                           | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request    |                                                                                  |
| Mechanical data                                        |                                                                                          |                                                                                  |
| Weight [g]                                             | 566.6                                                                                    |                                                                                  |
| Materials                                              | stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm |                                                                                  |
| Materials (wetted parts)                               | Al2O3 (ceramics); FKM; stainless steel (316L/1.4404)                                     |                                                                                  |
| Min. pressure cycles                                   | 100 million                                                                              |                                                                                  |
| Process connection                                     | threaded connection G 1/2 external thread                                                |                                                                                  |
| Restrictor element integrated                          | no (can be retrofitted)                                                                  |                                                                                  |
| Displays / operating elements                          |                                                                                          |                                                                                  |
| Display                                                | Display unit                                                                             | 2 x LED, green                                                                   |
|                                                        | switching status                                                                         | LED, yellow                                                                      |
|                                                        | switch points                                                                            | LED ring, red                                                                    |
|                                                        | function display                                                                         | alphanumeric display, red 4-digit                                                |
|                                                        | measured values                                                                          | analogue display, 0...350° rotatable, pointer not visible when unit disconnected |
|                                                        | measured values                                                                          | alphanumeric display, red 4-digit                                                |
| With scale                                             | yes                                                                                      |                                                                                  |
| Extended display range (max.)                          | 1.6 bar                                                                                  | 23.2 psi                                                                         |
| Remarks                                                |                                                                                          |                                                                                  |
| Remarks                                                | switch point accuracy in the extended display range: 1.5 % of the span                   |                                                                                  |
| Pack quantity                                          | 1 pcs.                                                                                   |                                                                                  |

# PG2457



## Pressure sensor with analogue display

PG-001-REB12-MFRKG/US/ /P

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1  
OUT2

switching output  
analogue output