



Volumni kabel

Cable/100m/PPU/5x0,34qmm/SF

No scale drawing available

Radni uvjeti

Temperatura okoline	[°C]	-30...80
---------------------	------	----------

Temperatura okoline (pokretna)	[°C]	-5...80
-----------------------------------	------	---------

Mehanički podaci

Težina	[g]	5092,2
--------	-----	--------

Opaske

Količina pakiranja	1 kom.
--------------------	--------

Električni priključak

Kabel: 100 m, PUR, crno, Ø 6 mm; visoko fleksibilan; 5 x 0,34 mm² (42 x Ø 0,1 mm), PVCKabel: 100 m, PUR / PVC, crno, Ø 6 mm; visoko fleksibilan; 5 x 0,34 mm² (42 x Ø 0,1 mm), PVC