

E12256



Volumni kabel

CABLE/100m/PVC/4x0,34/ORANGE



Radni uvjeti

Temperatura okoline	[°C]	-25...100
Temperatura okoline (pokretna)	[°C]	5...100

Mehanički podaci

Težina	[g]	3559,5
--------	-----	--------

Opaske

Količina pakiranja	1 kom.
--------------------	--------

Električni priključak

Kabel: 100 m, PVC, Narančasto, Ø 4,9 mm; 4 x 0,34 mm² (42 x Ø 0,1 mm)