


# DX2023



## Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/PNP OUT/AC/DC




Product characteristics	
Dimensions	[mm] 48 x 112 x 116
Application	
Application	universal evaluation and display for all physical units which can be derived from pulse sequences
Electrical data	
Frequency AC	[Hz] 50...60
Operating voltage	[V] 115...230 AC / 18...30 DC
Current consumption	[mA] 100
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 4
Inputs	
Number of digital inputs	2
Outputs	
Number of digital outputs	4
Overload protection	yes
Operating conditions	
Ambient temperature	[°C] -20...60
Storage temperature	[°C] -25...70
Protection	IP 65
Protection rating terminals	IP 20
Tests / approvals	
EMC	EN 61000-6-2
	EN 61000-6-3
	EN 61000-6-4



## Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/PNP OUT/AC/DC

Mechanical data		
Weight	[g]	352
Type of mounting		panel cutout: 91 x 43 mm
Dimensions	[mm]	48 x 112 x 116
Materials		Noryl UL94-V-0
Displays / operating elements		
Display	colour display	full graphic LCD display, touch screen
Electrical connection		
screw terminals:		
Connection		



NC: not used