


AC1345



Gateway PROFIBUS DP AS-Interface dengan PLC

ControllerE 1Mstr DP RS232

Produk tidak tersedia - entri arsip



1 Display



Aplikasi		
Aplikasi	pengontrol terdesentralisasi; Gateway PROFIBUS DP	
Data kelistrikan		
Tegangan pengoperasian	[V]	24 DC
Peringkat isolasi	[V]	500
Konsumsi arus	[mA]	< 500
Konsumsi arus maks. dari AS-i	[mA]	10
Konsumsi daya maks.	[VA]	10
Jumlah master AS-i		1
Pemisahan potensial		ya
Interface		
Interface komunikasi	RS232; PROFIBUS	
PROFIBUS		
Standar transmisi	EN 50170	



Gateway PROFIBUS DP AS-Interface dengan PLC

ControllerE 1Mstr DP RS232

Laju transmisi	12 MBaud
Protokol	Profibus DP
Tipe penggunaan	transmisi data
Catatan tentang interface	fungsi diagnostik

RS232

Jumlah interface R232	1
Laju transmisi	9600...115200 Baud
Tipe konektor	RJ11
Tipe penggunaan	pemrograman
Catatan tentang interface	diisolasi secara elektrik

Kondisi pengoperasian

Suhu sekitar [°C]	0...60
Suhu penyimpanan [°C]	-20...70
Kelembapan udara relatif maks. [%]	95
Perlindungan	IP 20

Klasifikasi AS-i

Versi AS-i	2.1
Profil master AS-i	M3

Data teknis

Casing	casing untuk pemasangan rel DIN
Dimensi [mm]	86 x 131 x 107
Material	aluminium; pelat baja galvanis

Elemen display/pengoperasian

Display	fungsi	2 x LED, merah
		2 x LED, hijau
		2 x LED, kuning
		display LCD grafis penuh

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Koneksi

