


DN1020



Suplai daya mode switch 24 V DC

POWER SUPPLY/24VDC/1,3A



Data kelistrikan

Tegangan nominal AC	[V]	< 230
Frekuensi nominal AC	[Hz]	50...60
Rentang tegangan input AC	[V]	100...240
Tegangan output DC	[V]	24...28
Kelas perlindungan		I; (IEC 61140)
Pelindung tegangan berlebih		ya; (< 40)
Tegangan output	[V]	dapat disesuaikan
Toleransi tegangan output	[%]	2
Arus output maks. pada tegangan output minimal	[A]	1.3
Jumlah sirkuit output		1
Sisa riak maks.	[mV]	50
Efisiensi (tegangan nominal 230 V AC / 50 Hz)	[%]	87.5
Derating	[W/K]	1 (60...70 °C)
Waktu buffering listrik (tegangan nominal 230 V AC / 50 Hz)	[ms]	190

Output

Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Kondisi pengoperasian

Suhu sekitar	[°C]	-10...70
Perlindungan		IP 20

Pengujian/persetujuan


EME	EN 61000-6-2	
	EN 61000-6-3	
MTTF	[ANN]	411



Suplai daya mode switch 24 V DC

POWER SUPPLY/24VDC/1,3A

Data teknis		
Berat	[g]	310.5
Tipe pemasangan		rel; (TH35 (EN 60715))
Dimensi	[mm]	83 x 45 x 96
Material		PC
Elemen display/pengoperasian		
Display	fungsi	LED, hijau
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
terminal klem pegas: ...2.5 mm ²		
Koneksi		



- 1 primer
2 sekunder