

Kabel koneksi dengan soket

ADOGH040SCS0005F03

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian	[V]	< 250 AC / < 300 DC
------------------------	-----	---------------------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis

Dimensi	[mm]	15 x 15 x 43
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, anti-percikan

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 5 m, PVC, oranye, Ø 5 mm; terkoneksi silang; 3 x 0.34 mm² (19 x Ø 0.15 mm)

Koneksi listrik - soket

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, anti-percikan; Torsi pengencangan: 0.5 Nm



E10419



Kabel koneksi dengan soket

ADOGH040SCS0005F03

Koneksi



BN =
BK =
BU =

Warna core :
coklat
hitam
biru