



Kabel koneksi dengan soket

ADOGH040MSS0015A04

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	< 250 AC / < 300 DC

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67

Data teknis		
Dimensi	[mm]	15 x 15 x 43
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel

Keterangan		
Jumlah paket		1 buah

Koneksi listrik		
Kabel: 15 m, PUR / PVC, oranye, Ø 5 mm; 4 x 0.25 mm² (32 x Ø 0.1 mm)		

Koneksi listrik - soket		
Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel		



E10435



Kabel koneksi dengan soket

ADOGH040MSS0015A04

Koneksi



BN =	Warna core :	coklat
BK =		hitam
BU =		biru
WH =		putih