



Kabel koneksi dengan soket

ADOGH040MSS07,5F03

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	10...55 DC
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67
Data teknis		
Dimensi	[mm]	15 x 15 x 43
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, anti-percikan
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 7.5 m, PVC, oranye, Ø 5 mm; terkoneksi silang; 3 x 0.34 mm² (19 x Ø 0.15 mm)		
Koneksi listrik - soket		

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, anti-percikan



E10471



Kabel koneksi dengan soket

ADOGH040MSS07,5F03

Koneksi



BN =
BK =
BU =

Warna core :
coklat
hitam
biru