

E10490



Kabel koneksi dengan soket

ADOGH040MSS0003A03

Produk tidak tersedia - entri arsip



Data kelistrikan		
Tegangan pengoperasian	[V]	< 250 AC / < 300 DC
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...90
Perlindungan		IP 67
Data teknis		
Dimensi	[mm]	15 x 15 x 43
Material		TPU
Material bodi detakan		TPU
Material mur		kuningan, berlapis nikel
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 3 m, PUR / PVC, oranye, Ø 5 mm; 3 x 0.34 mm²		
Koneksi listrik - soket		

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E10490



Kabel koneksi dengan soket

ADOGH040MSS0003A03

Koneksi



BN =
BK =
BU =

Warna core :
coklat
hitam
biru