

E10512



Kabel koneksi dengan soket

ADOAH040MSS0005A03

Produk tidak tersedia - entri arsip



Data kelistrikan

Tegangan pengoperasian [V] < 250 AC / < 300 DC

Kondisi pengoperasian

Suhu sekitar [°C] -25...90

Perlindungan IP 67

Data teknis

Dimensi [mm] 27 x 15 x 39

Material TPU

Material bodi detakan TPU

Material mur kuningan, berlapis nikel

Keterangan


Jumlah paket 1 buah

Koneksi listrik

Kabel: 5 m, PUR / PVC, oranye, Ø 5 mm; 3 x 0.34 mm²

Koneksi listrik - soket

Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: TPU; Penguncian: kuningan, berlapis nikel



E10512



Kabel koneksi dengan soket

ADOAH040MSS0005A03

Koneksi



BN =	Warna core :	coklat
BK =		hitam
BU =		biru